



TXA111

IP20

**Power supply 30V DC 320 mA**

**Technical properties**

**Architecture**

Bus system EIB

**Configuration**

Number of modules 4

**Connectivity**

Bus lines 1

**Main electrical features**

Frequency 50/60 Hz

**Voltage**

Output voltage 30 V

Output voltage 28...32 V

Filtered output voltage 30V +/- 2V

**Electric current**

Output current max. 320 mA

Output intensity 320 mA

**Dimensions**

Depth of installed product 64 mm

Height of installed product 90 mm

Length 64 mm

Width of installed product 72 mm

**Power**

Total power loss under IN 15 W

**Materials**

RAL colour RAL 7035 - Light grey

**Connection**

Connection cross-sect. flexible conductor 0,75 / 2,5mm<sup>2</sup>

Connection cross-sect. rigid cable 0,75 / 2.5mm<sup>2</sup>

Conductor cross-section (flexible) 0.75...2.5 mm<sup>2</sup>

Conductor cross-section (rigid) 0.75...2.5 mm<sup>2</sup>

Type of connection quick connect

**Use**

**Use conditions**

---

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C

---