



TXA111



## Power supply 30V DC 320 mA

### Technical properties

#### Architecture

Bus system	EIB
Fixing mode	Din-Rail

#### Configuration

Number of modules	4
-------------------	---

#### Connectivity

Bus lines	1
-----------	---

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Output voltage	30 V
Output voltage	28...32 V
Filtered output voltage	30V +/- 2V

#### Electric current

Output current	max. 320 mA
Output intensity	320 mA

#### Dimensions

Depth of installed product	64 mm
Height of installed product	90 mm
Length	64 mm
Width of installed product	72 mm

#### Power

Total power loss under IN	15 W
---------------------------	------

#### Materials

Colour	stone grey
RAL colour	RAL 7035 - Light grey

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Type of connection	quick connect

**Use**

Differentiation characteristic 1 - Sales

with labelling field

**Safety**

Protection index IP

IP20

**Use conditions**

Operating temperature

-5...45 °C

Storage/transport temperature

-20...70 °C