



TXA624D



OUTPUT DEVICE FOR 4 SH/BLINDS 24V DC 6A/ NE

Technical properties

Architecture

Bus system	KNX
Number of blinds/shutters outputs	4
Fixing mode	REG

Functions

Bus module detachable	No
-----------------------	----

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Indicator lamp	yes
Manual selection switches / push-buttons	4 manual operation buttons for up/down per channel/device

Main electrical features

Rated current	6 A
---------------	-----

Voltage

Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Electric current

Bus current consumption (data transfer)	5 mA
Bus current consumption (idle)	3 mA
Number of entry circuits	0
Maximum switching current	6 A
Switching current at 24 V=	6 A

Dimensions

Width of rail mounted device (RMD)	4 modules
Height	90 mm

Power

Contact rating with 230 V in AC1	1200 W
----------------------------------	--------

Materials

Colour	light grey
--------	------------

Connection

Conductor cross-section (flexible)	0.75...2.5 mm ²
------------------------------------	----------------------------

Conductor cross-section (rigid)	0.75...2.5 mm ²
Number of contacts	4
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Settings	
Supported configuration modes	system
Scope of delivery	
Bus connection included	Yes
Equipment	
Modular expandability	No
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX