



VD102NT

Sm.distr.,VD/IC<sup>2</sup>,surface,1row,2M,IP30,no terminals,AUS,without door

### Technical properties

#### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

#### Electric current

Rated current	63 A
---------------	------

#### Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

Has neutral terminal block	No
----------------------------	----

Has earthing terminal block	No
-----------------------------	----

Has mounting plate	No
--------------------	----

#### Capacity

Number of modules	2
-------------------	---

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	163,50 mm
--------	-----------

Width	45,50 mm
-------	----------

Depth	71 mm
-------	-------

Number of width units	2
-----------------------	---

#### Cover, door

Number of cabinet doors	0
-------------------------	---

Number of locks	0
-----------------	---

#### Materials

Material	Plastic
----------	---------

RAL code	9010
----------	------

Colour	Pure white
--------	------------

Ultraviolet-resistant	No
-----------------------	----

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	750 °C