



VD103NT

Sm.distr.,VD/IC²,surface,1row,3M,IP30,no terminals,AUS,without door

Technical properties

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block No

Has earthing terminal block No

Has mounting plate No

Capacity

Number of modules 3

Functions

With conduit inlets Yes

Dimensions

Height 163,50 mm

Width 63,50 mm

Depth 71 mm

Number of width units 3

Cover, door

Number of cabinet doors 0

Number of locks 0

Materials

Material Plastic

RAL code 9010

Colour Pure white

Ultraviolet-resistant No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	750 °C