



VD104NT

Sm.distr.,VD/IC²,surface,1row,4M,IP30,no terminals,AUS,without door

Technical properties

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	No
Has earthing terminal block	No
Has mounting plate	No

Capacity

Number of modules	4
-------------------	---

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	163,50 mm
Width	81,50 mm
Depth	71 mm
Number of width units	4

Cover, door

Number of cabinet doors	0
Number of locks	0

Materials

Material	Plastic
RAL code	9010
Colour	Pure white
Ultraviolet-resistant	No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP30
Locking type	Without lock
Glow wire test	750 °C
