



VD106PT

Sm.distr.,VD/IC²,surface,1row,6M,IP40,no terminals,AUS,white door

Technical properties

Voltage

Nominal voltage 400 - 400 V

Installation, mounting

Suitable for outdoor usage No

Mounting on Surface mounting

Electric current

Rated current 63 A

Equipment

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block No

Has earthing terminal block No

Has mounting plate No

Capacity

Number of modules 6

Functions

With conduit inlets Yes

Dimensions

Height 170 mm

Width 134,50 mm

Depth 91 mm

Number of width units 6

Cover, door

Number of cabinet doors 1

Number of locks 0

Door/cover is transparent No

Materials

Material Plastic

RAL code 9010

Colour Pure white

Ultraviolet-resistant No

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock, Without lock
Glow wire test	650 °C
