



VD110PT

**Sm.distr.,VD/IC<sup>2</sup>,surface,1row,10M,IP40,MS-terminals,N+PE,AUS,white door**

**Technical properties**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Surface mounting

**Electric current**

Rated current 63 A

**Equipment**

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block Yes

Has earthing terminal block Yes

Has mounting plate No

**Capacity**

Number of modules 10

**Functions**

With conduit inlets Yes

**Dimensions**

Height 170 mm

Width 206,50 mm

Depth 91 mm

Number of width units 10

**Cover, door**

Number of cabinet doors 1

Number of locks 0

Door/cover is transparent No

**Materials**

Material Plastic

RAL code 9010

Colour Pure white

Ultraviolet-resistant No

**Safety**

---

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock, Without lock
Glow wire test	650 °C

---