



VE110H

vector,IP65,8-10M,UV-stabil,DC/AC,with knockouts

Technical properties

Connection

Number of conduit inlets	6
--------------------------	---

Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	Yes
----------------------------	-----

Mounting on	Surface mounting
-------------	------------------

Electric current

Rated current	63 A
---------------	------

Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

Has neutral terminal block	Yes
----------------------------	-----

Has earthing terminal block	Yes
-----------------------------	-----

Has mounting plate	No
--------------------	----

Capacity

Number of modules	10
-------------------	----

Functions

With conduit inlets	Yes
---------------------	-----

Dimensions

Height	210 mm
--------	--------

Width	237 mm
-------	--------

Depth	114 mm
-------	--------

Number of width units	10
-----------------------	----

Cover, door

Number of cabinet doors	1
-------------------------	---

Number of locks	0
-----------------	---

Door/cover is transparent	Yes
---------------------------	-----

Materials

Material	Plastic
----------	---------

RAL code	7035
Colour	Light grey
Ultraviolet-resistant	Yes

Safety

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP65
Locking type	Snap on lock, Without lock
Glow wire test	850 °C