



VF104PT

**Small distributor,golf,flush,1row,4M,IP40,MS-terminal,Australia,N+PE,white door**

### Technical properties

#### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
Mounting on	Flush mounting

#### Electric current

Rated current	80 A
---------------	------

#### Equipment

Number of rails	1
Number of rows	1
Number of section in width	1
With lock	No
Has neutral terminal block	Yes
Has earthing terminal block	Yes
Has mounting plate	No

#### Capacity

Number of modules	4
-------------------	---

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	225 mm
Width	204 mm
Depth	97,50 mm
Built-in height	189 mm
Built-in width	170 mm
Built-in depth	72 mm
Number of width units	4

#### Cover, door

Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	No

#### Materials

Material	Plastic
----------	---------

RAL code	9010
Colour	Pure white
Ultraviolet-resistant	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Locking type	Snap on lock, Without lock
Glow wire test	850 °C