



VF108TT

**Small distributor,golf,flush,1row,8M,IP40,MS-terminal,AUS,N+PE,transparent door**

### Technical properties

#### Voltage

Nominal voltage	400 - 400 V
-----------------	-------------

#### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Flush mounting
-------------	----------------

#### Electric current

Rated current	80 A
---------------	------

#### Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

Number of section in width	1
----------------------------	---

With lock	No
-----------	----

Has neutral terminal block	Yes
----------------------------	-----

Has earthing terminal block	Yes
-----------------------------	-----

Has mounting plate	No
--------------------	----

#### Capacity

Number of modules	8
-------------------	---

#### Functions

With conduit inlets	Yes
---------------------	-----

#### Dimensions

Height	225 mm
--------	--------

Width	275 mm
-------	--------

Depth	97,50 mm
-------	----------

Built-in height	189 mm
-----------------	--------

Built-in width	242 mm
----------------	--------

Built-in depth	72 mm
----------------	-------

Number of width units	8
-----------------------	---

#### Cover, door

Number of cabinet doors	1
-------------------------	---

Number of locks	0
-----------------	---

Door/cover is transparent	Yes
---------------------------	-----

#### Materials

Material	Plastic
----------	---------

RAL code	9010
Colour	Pure white
Ultraviolet-resistant	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Locking type	Snap on lock, Without lock
Glow wire test	850 °C