



VF118PT

**Small distributor,golf,flush,1row,18M,IP40,MS-terminal,Australia,N+PE,white door**

**Technical properties**

**Voltage**

Nominal voltage 400 - 400 V

**Installation, mounting**

Suitable for outdoor usage No

Mounting on Flush mounting

**Electric current**

Rated current 80 A

**Equipment**

Number of rails 1

Number of rows 1

Number of section in width 1

With lock No

Has neutral terminal block Yes

Has earthing terminal block Yes

Has mounting plate No

**Capacity**

Number of modules 18

**Functions**

With conduit inlets Yes

**Dimensions**

Height 293 mm

Width 460 mm

Depth 97,50 mm

Built-in height 257 mm

Built-in width 426 mm

Built-in depth 72 mm

Number of width units 18

**Cover, door**

Number of cabinet doors 1

Number of locks 0

Door/cover is transparent No

**Materials**

Material Plastic

RAL code	9010
Colour	Pure white
Ultraviolet-resistant	No

**Safety**

Protection class	Isolation class II
Impact resistance IK	IK07
Ingress Protection (IP) class	IP40
Locking type	Snap on lock, Without lock
Glow wire test	850 °C