



VF218PZE



Small distributor,golf,flush,MM,2row,36M,white door, slotted

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Configuration

Number of modules	36
-------------------	----

Compatibility

Suitable for lightning protection	No
-----------------------------------	----

Dimensions

Insertion depth	72 mm
Depth of wall niche	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	418 mm
Installation height	382 mm
Width of installed product	460 mm
Width in division units	18
Thickness of sidewall material	3 mm
Built-in width	426 mm

Cover, door

Material thickness cover	3 mm
Type of door closing	Latch
Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	With Notch
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings	
Enclosure type	Distributor empty cabinet
Equipment	
Number of units	18
Number of rows	2
Quantity of rails	2
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	No
Neutral terminal block	No
Signal passing door	Yes
Standards	
GWT Glow wire test	650 °C
Safety	
IK protection code against mechanical impacts	IK07
REACH conform	No
RoHS conform	Yes
Halogen free	No