



VF318PT



Small distributor,golf,flush,3row,54M,IP40,MS-terminal,Australia,N+PE,white door

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	54
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Insertion depth	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	543 mm
Width of installed product	460 mm
Width in division units	18
Built-in height	507 mm
Built-in width	426 mm

Cover, door

Type of door closing	Latch
Identification od protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
Type of surface treatment	untreated

Installation, mounting	
Suitable for outdoor use	No
Settings	
Enclosure type	Distributor empty cabinet
Equipment	
Number of rows	3
Quantity of section in width	1
Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Safety	
Protection class	isol.class II
Use conditions	
Operating temperature	-25...40 °C