



VS104PT



Small distributor,golf,surface,1row,IP40,4M,MS-terminal,AUS,N+PE,white door

Technical properties

Functions

With a pipe-in lead Yes

Configuration

Number of modules 4

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 80 A

Dimensions

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 184 mm

Width of installed product 138 mm

Width in division units 4

Cover, door

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

Standards

GWT Glow wire test	650 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------