



VS118PT



Small distributor,golf,surface,1row,IP40,18M,MS-terminal,AUS,N+PE,white door

Technical properties

Functions

With a pipe-in lead Yes

Configuration

Number of modules 18

Main electrical features

Nominal voltage 400 V

Electric current

Rated current 80 A

Dimensions

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 252 mm

Width of installed product 390 mm

Width in division units 18

Cover, door

Identification of protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door No

Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

Installation, mounting

Suitable for outdoor use No

Settings

Enclosure type Distributor empty cabinet

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

Standards

GWT Glow wire test	650 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------