



VS118PT



Small distributor,golf,surface,1row,IP40,18M,MS-terminal,AUS,N+PE,white door

Technical properties

Functions

With a pipe-in lead	Yes
---------------------	-----

Configuration

Number of modules	18
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	80 A
---------------	------

Dimensions

Depth of installed product	99 mm
Internal depth	99 mm
Height of installed product	252 mm
Width of installed product	390 mm
Width in division units	18

Cover, door

Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Settings

Enclosure type	Distributor empty cabinet
----------------	---------------------------

Equipment

Number of rows	1
Quantity of section in width	1
Quantity of rails	1
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

Standards

GWT Glow wire test	650 °C
--------------------	--------

Safety

IK protection code against mechanical impacts	07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	No
Impact strength	IK07

Use conditions

Operating temperature	-25...40 °C
-----------------------	-------------