



VS312TT



**Small distributor,golf,surface,3row,IP40,36M,MS-terminal,AUS,N+PE,transpare door**

#### Technical properties

##### Architecture

Fixing mode surface-mounting

##### Functions

With a pipe-in lead Yes

##### Configuration

Number of modules 36

##### Main electrical features

Nominal voltage 400 V

##### Electric current

Rated current 80 A

##### Dimensions

Depth of installed product 99 mm

Internal depth 99 mm

Height of installed product 500 mm

Width of installed product 282 mm

Width in division units 12

##### Cover, door

Identification od protection index 40

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door locking without

Door leave single

Cover type Door

Transparent cover or door Yes

##### Materials

Colour white

RAL colour RAL 9010 - Pure white

Material plastic

Type of surface treatment untreated

##### Installation, mounting

Suitable for outdoor use No

**Equipment**

Number of rows	3
Quantity of section in width	1
Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	Yes
Signal passing door	Yes

**Safety**

Protection index IP	IP40
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes

**Use conditions**

Operating temperature	-25...40 °C
-----------------------	-------------