



VT09S

## Technical properties

### Connection

Number of conduit inlets	16
--------------------------	----

### Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

### Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Mounting on	Surface mounting
-------------	------------------

### Equipment

Number of rails	1
-----------------	---

Number of rows	1
----------------	---

### Capacity

Number of modules	9
-------------------	---

### Dimensions

Height	250 mm
--------	--------

Width	259 mm
-------	--------

Depth	71 mm
-------	-------

Built-in depth	70 mm
----------------	-------

Number of width units	9
-----------------------	---

### Cover, door

Number of locks	0
-----------------	---

Door/cover is transparent	No
---------------------------	----

### Connectivity

Mounting type	Screw mounting
---------------	----------------

### Materials

Material	Steel
----------	-------

RAL code	9002
----------	------

Colour	Grey white
--------	------------

### Safety

Protection class	Isolation class I
------------------	-------------------

Impact resistance IK	IK05
----------------------	------