



9M 1Row DIN Surface Metal BOX, 7.5M Door

Technical properties

Connection

Number of conduit inlets	16
--------------------------	----

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
Mounting on	Surface mounting

Equipment

Number of rails	1
Number of rows	1

Capacity

Number of modules	9
-------------------	---

Dimensions

Height	250 mm
Width	259 mm
Depth	71 mm
Built-in depth	70 mm
Number of width units	9

Cover, door

Number of cabinet doors	1
Number of locks	0
Door/cover is transparent	No

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
RAL code	9002
Colour	Grey white

Safety

Protection class	Isolation class I
Impact resistance IK	IK05
Ingress Protection (IP) class	IP30

