



VT12F

12M 1Row DIN Flush Metal BOX, No Door

Technical properties

Connection

Number of conduit inlets	16
--------------------------	----

Voltage

Nominal voltage	230 - 415 V
-----------------	-------------

Installation, mounting

Suitable for outdoor usage	No
----------------------------	----

Equipment

Number of rails	1
Number of rows	1
Has mounting plate	No

Capacity

Number of modules	12
-------------------	----

Dimensions

Height	304 mm
Width	354 mm
Depth	10 mm
Built-in width	304 mm
Built-in depth	60 mm
Number of width units	12

Cover, door

Number of locks	0
Door/cover is transparent	No

Connectivity

Mounting type	Screw mounting
---------------	----------------

Materials

Material	Steel
RAL code	9002
Colour	Grey white

Safety

Protection class	Isolation class I
Impact resistance IK	IK05