



VYMBV-P

panel only - enclosure Victoria

Technical properties

Architecture

Intended door position right

Configuration

Number of modules 0

Compatibility

Suitable for lightning protection No

Dimensions

Insertion depth 278 mm

Depth of installed product 278 mm

Internal depth 276 mm

Height of installed product 430 mm

Width of installed product 488 mm

Thickness of sidewall material 1 mm

Cover, door

Identification of protection index 23

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door leave single

Cover type none / closed

Transparent cover or door No

Materials

Copper weight of the product 0 kg

Colour light grey

RAL colour RAL 7035 - Light grey

Material quality Steel

Surface appearance satin finish

Installation, mounting

Suitable for ground mounting Yes

Equipment

Quantity of rails 0

On/Off switch No

Number of openings for flange plates 0

Extension possible

No

Standards

Approvals

AS/NZS 61439-3

Safety

IK protection code against mechanical impacts

IK05

Protection class

isol.class I

Glow wire test

according to AS/NZS 61439-1

Fire resistance

-