



VYMBV-P

**panel only - enclosure Victoria**

**Technical properties**

**Architecture**

Intended door position right

**Configuration**

Number of modules 0

**Compatibility**

Suitable for lightning protection No

**Dimensions**

Insertion depth 278 mm

Depth of installed product 278 mm

Internal depth 276 mm

Height of installed product 430 mm

Width of installed product 488 mm

Thickness of sidewall material 1 mm

**Cover, door**

Identification of protection index 23

Interlockable No

Number of keylock of the door 0

Cover type Closed (plain)

Door leave single

Cover type none / closed

Transparent cover or door No

**Materials**

Copper weight of the product 0 kg

Colour light grey

RAL colour RAL 7035 - Light grey

Material quality Steel

Surface appearance satin finish

**Installation, mounting**

Suitable for ground mounting Yes

**Equipment**

Quantity of rails 0

On/Off switch No

Number of openings for flange plates 0

Extension possible

No

---

**Standards**

Approvals

AS/NZS 61439-3

---

**Safety**

IK protection code against mechanical impacts

IK05

Protection class

isol.class I

Glow wire test

according to AS/NZS 61439-1

Fire resistance

-