



VYMBV-P

**panel only - enclosure Victoria**

**Technical properties**

**Architecture**

Intended door position	right
------------------------	-------

**Configuration**

Number of modules	0
-------------------	---

**Compatibility**

Suitable for lightning protection	No
-----------------------------------	----

**Dimensions**

Insertion depth	278 mm
Depth of installed product	278 mm
Internal depth	276 mm
Height of installed product	430 mm
Width of installed product	488 mm
Thickness of sidewall material	1 mm

**Cover, door**

Identification of protection index	23
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door leave	single
Cover type	none / closed
Transparent cover or door	No

**Materials**

Copper weight of the product	0 kg
Colour	light grey
RAL colour	RAL 7035 - Light grey
Material quality	Steel
Surface appearance	satin finish

**Installation, mounting**

Suitable for ground mounting	Yes
------------------------------	-----

**Equipment**

Quantity of rails	0
On/Off switch	No
Number of openings for flange plates	0

Extension possible

No

---

**Standards**

Approvals

AS/NZS 61439-3

---

**Safety**

IK protection code against mechanical impacts

IK05

Protection class

isol.class I

Glow wire test

according to AS/NZS 61439-1

Fire resistance

-