



VZ093

Spare door,vector,IP65 for VE110

Technical properties

Architecture

Intended door position	left
Fixing mode	Clamping

Dimensions

Depth of installed product	13.5 mm
Internal depth	13.5 mm
Height of installed product	132 mm
Width of installed product	208 mm
Built-in height	132 mm
Built-in width	208 mm

Cover, door

Material thickness cover	2.4 mm
Number of keylock of the door	0
Door type for switch gear cabinet	Stop door
Door leave	single
Transparent cover or door	Yes

Materials

Colour	stone grey
Colour	transparent
Material	plastic
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Equipment

Number of rows	1
Quantity of section in width	1
Number of keys	1

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	Yes

RoHS conform	Yes
Halogen free	Yes
Use conditions	
Operating temperature	-25...40 °C