



VZ098

Spare door,vector,IP65 for VE312

Technical properties

Architecture

Intended door position	left
------------------------	------

Dimensions

Depth of installed product	17 mm
Internal depth	17 mm
Height of installed product	398 mm
Width of installed product	280 mm
Built-in height	398 mm
Built-in width	280 mm

Cover, door

Material thickness cover	2.9 mm
Type of door closing	Latch
Number of keylock of the door	0
Door type for switch gear cabinet	Stop door
Door leave	single
Transparent cover or door	Yes

Materials

Colour	stone grey
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	Yes
--------------------------	-----

Equipment

Number of rows	3
Quantity of section in width	1
Number of keys	1

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK08
Protection class	isol.class II
REACH conform	Yes
RoHS conform	Yes
Halogen free	Yes

Use conditions

Operating temperature

-25...40 °C