



VZ604N

Door,golf,white,accessory,for VF/VS212

Technical properties

Architecture

Intended door position	left
Fixing mode	Clamping

Dimensions

Depth of installed product	16.5 mm
Internal depth	16.5 mm
Height of installed product	375 mm
Width of installed product	280 mm
Built-in height	375 mm
Built-in width	280 mm

Cover, door

Type of door closing	Latch
Number of keylock of the door	0
Door type for switch gear cabinet	Stop door
Door leave	single
Transparent cover or door	No

Materials

Colour	RAL 9010
Colour	white
RAL colour	RAL 9010 - Pure white
Material	plastic
Surface appearance	glossy
Type of surface treatment	untreated

Installation, mounting

Suitable for outdoor use	No
--------------------------	----

Equipment

Number of rows	2
Quantity of section in width	1

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

IK protection code against mechanical impacts	IK07
Protection index IP	IP40

Protection class

isol.class II

Use conditions

Operating temperature

-25...40 °C