



VZ608N

Door,golf,white,accessory,for VF/VS218

Technical properties

Architecture

| | |
|------------------------|----------|
| Intended door position | left |
| Fixing mode | Clamping |

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 16.5 mm |
| Internal depth | 16.5 mm |
| Height of installed product | 375 mm |
| Width of installed product | 388 mm |
| Built-in height | 375 mm |
| Built-in width | 388 mm |

Cover, door

| | |
|-----------------------------------|-----------|
| Type of door closing | Latch |
| Number of keylock of the door | 0 |
| Door type for switch gear cabinet | Stop door |
| Door leave | single |
| Transparent cover or door | No |

Materials

| | |
|---------------------------|-----------------------|
| Colour | RAL 9010 |
| Colour | white |
| RAL colour | RAL 9010 - Pure white |
| Material | plastic |
| Surface appearance | glossy |
| Type of surface treatment | untreated |

Installation, mounting

| | |
|--------------------------|----|
| Suitable for outdoor use | No |
|--------------------------|----|

Equipment

| | |
|------------------------------|---|
| Number of rows | 2 |
| Quantity of section in width | 1 |

Standards

| | |
|-------------------------|---------------|
| European directive WEEE | not concerned |
|-------------------------|---------------|

Safety

| | |
|---|------|
| IK protection code against mechanical impacts | IK07 |
| Protection index IP | IP40 |

Protection class

isol.class II

Use conditions

Operating temperature

-25...40 °C