



VZ624N

Door,golf,transparent,accessory,for VF/VS212

Technical properties

Architecture

Intended door position left

Dimensions

Depth of installed product 16.5 mm

Internal depth 16.5 mm

Height of installed product 375 mm

Width of installed product 280 mm

Built-in height 375 mm

Built-in width 280 mm

Cover, door

Number of keylock of the door 0

Door leave single

Transparent cover or door Yes

Materials

Material plastic

Type of surface treatment untreated

Installation, mounting

Suitable for outdoor use No

Equipment

Number of rows 2

Quantity of section in width 1

Standards

European directive WEEE not concerned

Safety

IK protection code against mechanical impacts IK07

Protection class isol.class II

REACH conform Yes

RoHS conform Yes

Halogen free Yes

Use conditions

Operating temperature -25...40 °C