



VZ626N

**Door,golf,transparent,accessory,for VF/VS412**

**Technical properties**

**Architecture**

Intended door position left

**Dimensions**

Depth of installed product 16.5 mm

Internal depth 16.5 mm

Height of installed product 645 mm

Width of installed product 280 mm

Built-in height 645 mm

Built-in width 280 mm

**Cover, door**

Number of keylock of the door 0

Door leave single

Transparent cover or door Yes

**Materials**

Material plastic

Type of surface treatment untreated

**Installation, mounting**

Suitable for outdoor use No

**Equipment**

Number of rows 4

Quantity of section in width 1

**Standards**

European directive WEEE not concerned

**Safety**

IK protection code against mechanical impacts IK07

Protection class isol.class II

REACH conform Yes

RoHS conform Yes

Halogen free Yes

**Use conditions**

Operating temperature -25...40 °C