



WBHP115

Allure Single GPO 15A

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V AC
-----------------	----------

Frequency	50 Hz
-----------	-------

Electric current

Rated current	15 A
---------------	------

Installation, mounting

Entries	cable entries bevelled
---------	------------------------

Mounting type	flush-mounted
---------------	---------------

Installation mode	for screw fastening
-------------------	---------------------

Connection

Type of connection	with screw terminals
--------------------	----------------------

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Equipment

Number of socket outlets switchable	1
-------------------------------------	---

Safety

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

Identification

Main design line	Allure
------------------	--------