



WBHP1R



Allure Single GPO 10A with round Earth

Technical properties

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Frequency

| | |
|-----------|------------|
| Frequency | 50 - 50 Hz |
|-----------|------------|

Voltage

| | |
|-----------------|-------------|
| Nominal voltage | 250 - 250 V |
|-----------------|-------------|

Connectivity

| | |
|---------------|----------------|
| Mounting type | Screw mounting |
|---------------|----------------|

Safety

| | |
|-------------------------------|------|
| Ingress Protection (IP) class | IP20 |
|-------------------------------|------|

Materials

| | |
|--------|-------|
| Colour | White |
|--------|-------|

Installation, mounting

| | |
|-------------|------------------|
| Mounting on | Surface mounting |
|-------------|------------------|

Equipment

| | |
|-----------------------------------|---------------------------------|
| Connector/plug type socket outlet | Australian standard AS/NZS 3112 |
| Rotated central insert | No |
| With hinged lid | No |

Accessories

| | |
|---------------------|----|
| Has labelling field | No |
|---------------------|----|

Capacity

| | |
|-------------------|---|
| Number of modules | 1 |
|-------------------|---|

Texts

| | |
|----------------|------------------|
| Imprint | Without imprint |
| Cover | Complete housing |
| Related Series | allure |