



WBHP2S-MB

Allure Double GPO Matt Black

Technical properties

Configuration

Number of modules 2

Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

Electric current

Rated current 10 A

Dimensions

Height 81 mm

Width 119 mm

Materials

Surface appearance matt

Installation, mounting

Entries cable entries bevelled

Mounting type flush-mounted

Installation mode for screw fastening

Connection

Type of connection with screw terminals

Scope of delivery

Scope of delivery supplied with standard tapered point 32 mm fixing screws

Equipment

Number of socket outlets switchable 2

With transparent product label holder No

Safety

RoHS conform Yes

Protection without enhanced contact protection

Identification

Main design line Allure