



WBHP2XS

Allure DGPO 10A with Extra Switch

Technical properties

Electric current

Rated current	10 A
---------------	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Safety

Impact resistance IK	IK08
Ingress Protection (IP) class	IP2X

Dimensions

Built-in depth flush-mounted boxes	20 mm
Height	82 mm
Width	120 mm
Depth	9,50 mm

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC), Thermoplastic

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Connectivity

Type of connection	Screw terminal
Mounting type	Screw mounting

Equipment

Connector/plug type socket outlet	Australian standard AS/NZS 3112
Rotated central insert	No
With hinged lid	No
With round protective earth pin	No
With signal lamp	No

Capacity

Number of modules	2
-------------------	---

Texts

Imprint	Without imprint
Cover	Full cover plate

