



WBHP2XS

### Allure DGPO 10A with Extra Switch

#### Technical properties

##### Configuration

Number of modules 2

##### Connectivity

With USB charging socket No

##### Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

##### Electric current

Rated current 10 A

##### Materials

Colour white

##### Installation, mounting

Installation mode for screw fastening

##### Connection

Type of connection with screw terminals

##### Equipment

Number of socket outlets switchable 2

With transparent product label holder No

##### Safety

Protection index IP IP2X

Protection without enhanced contact protection