



WBHP2XS-MB

**Allure DGPO 10A with Extra Switch MB**

**Technical properties**

**Configuration**

Number of modules 2

**Main electrical features**

Nominal voltage 250 V AC

Frequency 50 Hz

**Electric current**

Rated current 10 A

**Installation, mounting**

Mounting type flush-mounted

Installation mode for screw fastening

**Connection**

Type of connection with screw terminals

**Equipment**

Number of socket outlets switchable 2

**Safety**

RoHS conform Yes

**Identification**

Main design line Allure