



WBHSV1

**Allure 1 Gang Switch Plate cw mechs**

**Technical properties**

**Electric current**

Rated current 16 A

**Installation, mounting**

Mounting on Flush mounting

**Frequency**

Frequency 50 - 50 Hz

**Materials**

Colour White

Surface finish Glossy

Material Polycarbonate (PC)

Treatment Untreated

**Identification**

Assembly arrangement Basic element with full cover plate

**Connectivity**

Mounting type Screw mounting

**Controls and indicators**

Number of buttons 1

**Dimensions**

Built-in depth 15 mm

Built-in depth flush-mounted boxes 15 mm

**Safety**

Ingress Protection (IP) class IP2X

Impact resistance IK IK08

**Texts**

Installation mode For screw fastening

Type of connection With screw terminals

Lighting Without lighting (cannot be illuminated)

Switch mode 2-way, with loop terminal