



WBHSV2



Allure 2 Gang Switch Plate cw mechs

Technical properties

Electric current

Rated current	16 A
---------------	------

Installation, mounting

Mounting on	Flush mounting
-------------	----------------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

Connectivity

Mounting type	Screw mounting
---------------	----------------

Controls and indicators

Number of buttons	2
-------------------	---

Dimensions

Built-in depth	15 mm
Built-in depth flush-mounted boxes	15 mm

Safety

Ingress Protection (IP) class	IP2X
Impact resistance IK	IK08

Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way, with loop terminal