



WBHSV2

## Allure 2 Gang Switch Plate cw mechs

### Technical properties

#### Electric current

Rated current	16 A
---------------	------

#### Installation, mounting

Mounting on	Flush mounting
-------------	----------------

#### Frequency

Frequency	50 - 50 Hz
-----------	------------

#### Materials

Colour	White
Surface finish	Glossy
Material	Polycarbonate (PC)
Treatment	Untreated

#### Identification

Assembly arrangement	Basic element with full cover plate
----------------------	-------------------------------------

#### Connectivity

Mounting type	Screw mounting
---------------	----------------

#### Controls and indicators

Number of buttons	2
-------------------	---

#### Dimensions

Built-in depth	15 mm
Built-in depth flush-mounted boxes	15 mm

#### Safety

Ingress Protection (IP) class	IP2X
Impact resistance IK	IK08

#### Texts

Installation mode	For screw fastening
Type of connection	With screw terminals
Lighting	Without lighting (cannot be illuminated)
Switch mode	2-way, with loop terminal