



WBHSV2-MW

## Allure 2 Gang Switch Plate cw mechs MW

### Technical properties

#### Architecture

Type of control unit rocker

#### Configuration

Switch mode 2 way, with loop terminal

#### Controls and indicators

Number of buttons 2

#### Main electrical features

Nominal voltage 250 V AC

Frequency 50 Hz

#### Electric current

Rated current 16 AX

#### Dimensions

Height 117 mm

Width 77 mm

#### Installation, mounting

Entries cable entries bevelled

Mounting type flush-mounted

Installation mode for screw fastening

#### Connection

Terminal terminals accommodate 4 x 1.5 mm<sup>2</sup> cable

Type of connection with screw terminals

Type of connection Screw connection

#### Scope of delivery

Scope of delivery supplied with standard tapered point 32 mm fixing screws

#### Safety

REACH conform Yes

RoHS conform Yes

Halogen free Yes

#### Identification

Main design line Allure