



WBMCAT5

Mechanism cat5 data

Technical properties

Configuration

Category / ports cat.5e

Connectivity

Outlet with straight outlet

Dimensions

Height 27 mm

Width 27 mm

Frequency

Transmission bandwidth max. 100 MHz

Resistance

Signal contact resistance < 20 mΩ

Insulation resistance min. 500 MΩ at 100 VDC

Materials

Colour code A and B according to TIA/EIA-568-C.2

Installation, mounting

Installation mode RotoLoc ®

Use conditions

Operating temperature -10...60 °C

Relative humidity (without condensation) 10...90 %

Identification

Main design line Mechanisms