



WBMCAT6

CAT6 Data Mech White

Technical properties

Configuration

Category / ports cat.6

Connectivity

Outlet with straight outlet

Dimensions

Depth 33 mm

Height 27 mm

Width 27 mm

Frequency

Transmission bandwidth max. 250 MHz

Resistance

Signal contact resistance < 20 mΩ

Insulation resistance min. 500 MΩ at 100 VDC

Materials

Colour code A and B according to TIA/EIA-568-C.2

Colour white

Surface appearance glossy

Installation, mounting

Installation mode RotoLoc ®

Safety

REACH conform Yes

RoHS conform Yes

Use conditions

Operating temperature -10...60 °C

Relative humidity (without condensation) 10...90 %

Identification

Main design line Mechanisms

With imprint Yes