



WBMCAT6-MW

**CAT6 Rotoloc Dat Mech MW**

**Technical properties**

**Configuration**

Category / ports cat.6

**Connectivity**

Outlet with straight outlet

**Dimensions**

Height 27 mm

Width 27 mm

**Frequency**

Transmission bandwidth max. 250 MHz

**Resistance**

Signal contact resistance < 20 mΩ

Insulation resistance min. 500 MΩ at 100 VDC

**Materials**

Colour code A and B according to TIA/EIA-568-C.2

**Installation, mounting**

Installation mode RotoLoc ®

**Safety**

REACH conform Yes

RoHS conform Yes

**Use conditions**

Operating temperature -10...60 °C

Relative humidity (without condensation) 10...90 %

**Identification**

Main design line Mechanisms