



WBMCAT6A

CAT6A Data Mech White

Technical properties

Connectivity

Outlet	with straight outlet
--------	----------------------

Dimensions

Height	27 mm
Width	27 mm

Frequency

Transmission bandwidth	max. 500 MHz
------------------------	--------------

Resistance

Signal contact resistance	< 20 mΩ
Insulation resistance	min. 500 MΩ at 100 VDC

Materials

Colour code A and B	according to TIA/EIA-568-C.2
---------------------	------------------------------

Installation, mounting

Installation mode	RotoLoc ®
-------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-10...60 °C
Relative humidity (without condensation)	10...90 %

Identification

Main design line	Mechanisms
------------------	------------