



WBMD400LED

AS ROTARY LED DIMMER

Technical properties

Functions

Soft startup	bulb-preserving soft startup
--------------	------------------------------

Main electrical features

Nominal voltage	240 V
Frequency	50 Hz

Voltage

Operating voltage	240 V~ +10%/-15%
-------------------	------------------

Fuse

Fuse	short-circuit proof
------	---------------------

Materials

Colour	white
Colour	white

LED control

Quantity LED lamps	max. 10
Dimmable 230 V LED lamps	10...120 W

Installation, mounting

Installation mode	RotoLoc ®
-------------------	-----------

Equipment

Dimming principle	phase cut-off
-------------------	---------------

Safety

REACH conform	No
Halogen free	No

Use conditions

Temperature	with overheating protection
Relative humidity (without condensation)	10...90 %

Identification

Main design line	Mechanisms
------------------	------------