




WBMSF3-MB



Mech 75VA 3 speed fan cont c/w capacitor MB

Technical properties

Voltage

Nominal voltage 250 - 250 V

Installation, mounting

Mounting on Flush mounting

Safety

Ingress Protection (IP) class IP20

Dimensions

Built-in depth flush-mounted boxes 46 mm

Materials

Colour Black

Treatment Varnished

Architecture

Control/operation element Rotative

Texts

Switch mode With neutral position "OFF": OFF-1-2-3

Type of connection With screw terminals