



WBP1R-BK

Technical properties

Configuration

Number of modules	1
-------------------	---

Main electrical features

Nominal voltage	250 V
Frequency	50 Hz

Electric current

Rated current	10 A
---------------	------

Dimensions

Height	77 mm
Width	117 mm

Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

Connection

Type of connection	with screw terminals
--------------------	----------------------

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Equipment

Number of socket outlets switchable	1
-------------------------------------	---

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes