



WBP1VXS

### Technical properties

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

#### Electric current

Rated current	10 A
---------------	------

#### Dimensions

Insertion depth	16 mm
Height	117 mm
Width	77 mm

#### Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

#### Connection

Type of connection	with screw terminals
--------------------	----------------------

#### Equipment

Number of socket outlets switchable	1
-------------------------------------	---

#### Safety

Protection index IP	IP20
---------------------	------