



WBP2CID

Premiere 10A horz twin GPO + ID

Technical properties

Configuration

| | |
|-------------------|---|
| Number of modules | 2 |
|-------------------|---|

Main electrical features

| | |
|-----------------|----------|
| Nominal voltage | 250 V AC |
| Frequency | 50 Hz |

Electric current

| | |
|---------------|------|
| Rated current | 10 A |
|---------------|------|

Dimensions

| | |
|-----------------|--------|
| Insertion depth | 11 mm |
| Height | 77 mm |
| Width | 117 mm |

Installation, mounting

| | |
|-------------------|------------------------|
| Entries | cable entries bevelled |
| Mounting type | flush-mounted |
| Installation mode | for screw fastening |

Scope of delivery

| | |
|-------------------|----------------------------------------------------------|
| Scope of delivery | supplied with standard tapered point 32 mm fixing screws |
|-------------------|----------------------------------------------------------|

Equipment

| | |
|-------------------------------------|---|
| Number of socket outlets switchable | 2 |
|-------------------------------------|---|

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
| REACH conform | Yes |
| RoHS conform | Yes |

Identification

| | |
|------------------|----------|
| Main design line | premiere |
|------------------|----------|