



WBP2VS-BK

Technical properties

Configuration

Number of modules	2
-------------------	---

Connectivity

With USB charging socket	Yes
Connectors / jacks	with 2 USB sockets type A

Main electrical features

Nominal voltage	250 V AC
Frequency	50 Hz

Voltage

Output voltage	5 V DC
----------------	--------

Electric current

Rated current	10 A
---------------	------

Fuse

Fuse	short-circuit and overload proof (electronic fuse)
------	--

Dimensions

Height	77 mm
Width	117 mm

Installation, mounting

Mounting type	flush-mounted
Installation mode	for screw fastening

Scope of delivery

Scope of delivery	supplied with standard tapered point 32 mm fixing screws
-------------------	--

Equipment

Number of socket outlets switchable	2
-------------------------------------	---

Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

Use conditions

Temperature	with overheating protection
-------------	-----------------------------